

STULZ

CLIMATE. CUSTOMIZED.



STULZ Custom Indoor AHU

Purpose-built solution for large and hyperscale data centers

STULZ air conditioning systems for mission critical applications - around the globe



For over 40 years we have been one of the world's leading manufacturers of air conditioning solutions for mission critical applications. We design, manufacture, deliver and support standard and customized precision cooling solutions, based on our client's specific requirements.

Our corporate headquarters are in Hamburg, Germany. With 21 subsidiaries, 11 production sites, and sales and service partners in over 140 countries, we make sure we are close to our customers wherever they are in the world.

STULZ USA handles all design, manufacturing and support for the North American market. Our North American headquarters and manufacturing plant is located in Frederick, Maryland, with a second manufacturing facility in Dayton, Tennessee.



Technical excellence

It is the combination of decades of experience and a continuous innovative spirit that makes STULZ unique. From engineers to customer advisers, we collaborate in close-knit teams to develop and continually optimize our cooling solutions throughout the development cycle. It should come as no surprise that our systems are extremely energy efficient, reliable, and durable, setting the new benchmark in mission critical applications around the globe.



High quality service worldwide

Our factory trained and experienced sales and service partners are located in over 140 countries. The resulting proximity to our customers allows fast response time. In addition, regular training courses and an active exchange of information ensures high quality and an extensive knowledge of all our products. This way, you can be sure your products are in the best hands and get the right maintenance.

STULZ Custom Indoor AHU – Meets users unique requirements

Breaking new ground

In applications where conventional systems have reached their limit, the STULZ Custom Indoor AHU surpasses these limitations. Footprint, power consumption, and capacity are no longer constrained in mission critical environments with this purpose-built solution.

The unique design provides larger supply area enabling maximum cooling density, and allowing taller server racks with denser IT load per unit area.

Solutions from scratch

In collaboration with the customer, we develop the design concept, manufacture and deliver the optimal solution.



Customized Modularity – Maximizing cooling density


The STULZ Custom Indoor AHU is a purpose-built, modular solution that meets users unique requirements. The unit is customizable to project-specific sizing and to various site conditions. The design concept with zero side access results in an increased cooling capacity per wall length. Furthermore the modularity increases the operational reliability through redundancy.



User Driven. Custom Designed. Purpose Built.

+ Design Concept

- Compact footprint yet maximized cooling capacity
- Higher efficiency and lower noise level
- Robust, extruded aluminum construction with various panel thicknesses, including a thermal break option
- Zero side clearance, space-efficient, modular design
- Operational reliability and redundancy through modularity
- Provides uniform cooling along the entire length of the aisle due to the larger area of supply air
- Supply air temperature within the range recommended by ASHRAE TC 9.9 guidelines




+ Efficiency


- Low pPUE values
- Higher efficiency and lower noise level
- Taller racks and higher heat loads possible because no raised floor is needed
- Lowest AER (Airflow Efficiency Ratio) values, and therefore air conduction with maximum efficiency
- Use of EC Fan technology for maximum efficiency


Efficiency through Custom Design

**Even temperature distribution
across supply air side**



**Uniform air velocity and
pressure across supply air side**





+ Customization

- Customization through various design options and cooling systems: Direct Expansion, Chilled Water, Direct Adiabatic, Free Cooling
- Multiple unit configurations: horizontal and vertical airflow, with and without duct system
- Ultrasonic Humidification for ducted and room mounted systems

+ Service / Maintenance

- Easy replacement of fans and filters
- Quick installation
- Factory trained and experienced sales and service partners in over 140 countries
- Lowest total cost of ownership (TCO)

Customized Modular Design for Maximum Cooling Density

With an extensive range of capacities and various unit configurations, STULZ offers the optimum solution for your individual requirements. With the STULZ Custom Indoor AHU, our customers receive a purpose-built solution that has been ideally suited for their application.

Varying purpose-built solutions

Horizontal AHU

The horizontal AHU is available with Direct Expansion (DX) and Chilled Water (CW) cooling. A specialized fan wall array ensures uniform airflow while meeting low power consumption requirements. Counterbalanced fan inlet backdraft dampers minimize air recirculation.



Modular Split AHU

The modular split AHU is available with DX and CW cooling. A vertical center split allows the modular AHU to fit in service elevators and maneuver within tight spaces. Its modular design allows easy reassembly and rewiring on-site using minimal labor (via frame and electrical connectors). The unit can also be deployed and/or operated as a half unit by only utilizing one side, therefore increasing redundancy.



Horizontal Stackable Fan/Coil Unit

The stackable chilled water (CW) fan coil unit reduces the total footprint while maintaining unit serviceability. The AHU is designed to easily stack units securely. Electrical connectors are provided between stacked units to reduce on-site installation time and cost.



Horizontal Split Sectional AHU

The horizontal split sectional AHU is available with DX and CW cooling. It is sized and split to fit in a standard freight shipping container for intermodal transportation. The unit can be easily reassembled and rewired on site using minimal labor (via frame and electrical connectors). Air discharge sound attenuators are provided for low sound applications.



The standardized model

WallFlow Custom AHU

The WallFlow Custom AHU is the standardized building block, based on a highly successful custom design that is deployed in multiple locations. Its design enables shorter delivery times while still offering various options or individual customization.



Technical Data		CAH-0100	CAH-0200
Cooling Capacity	kW	100	200
Airflow	ft ³ /min	12,500	25,000
Dimensions (W x H x D)	mm	1,501.1 × 2,400.3 × 1,559.6	2999.7 × 2,400.3 × 1,559.6
	in	59.1 × 94.5 × 61.4	118.1 × 94.5 × 61.4

Options for customization

Tailor-made solutions for data centers are achieved by numerous options and equipment versions:


- Horizontal or vertical orientation
- Various voltages available in 50/60 Hz designs
- STULZ E² microprocessor with a range of BMS interface
- Different filter options available; MERV-8, 11, 14
- Stainless steel dual sloped construction drain pan
- Door interlocking
- Backdraft and control dampers
- Aluminum frame construction
- Various valves available:
 - Energy valve
 - PICV (Pressure independent control valve)
 - 2-way or 3-way control valves
- Steam canister humidification
- Built-in UPS for unit control
- Dual power with auto transfer switch
- And more!

STULZ E² Control and Monitoring

- Configurable operating modes for maximum efficiency and reliability
- Multiple I/O capabilities for all major components to optimize control for energy savings
- Controller UPS available
- Suitable for connection to all common BMS systems
- Static pressure control provides even airflow, on demand at any room position, as well as precise control for containment




EC Fan



- Variable speed-controlled
- Nominal airflow rate at a fan speed optimized for partial load operation
- Multiple EC fan sizes available
- Increased airflow in each size
- Easy and fast replacement of fans and filters through front access
- Aluminum and composite blade options

PICV

- Dynamic load balance across all operating conditions
- Eliminates problems associated with low delta T syndrome
- Precisely matches design requirements for capacity and delta T
- Maximizes energy savings of variable flow systems while addressing unique control challenges



Globally close to you

As a company with locations across the globe, we have what it takes to provide data center operators, planners, and companies working in the highly-dynamic world of information technology (ICT and IT), with professional advice whenever and wherever they require it.

Since 1974, STULZ has seen continual international expansion of its air conditioning technology business, specializing in cooling data center and other mission critical installations. STULZ employs over 2,400 people worldwide in 20 subsidiaries and 10 production facilities in China, Europe, India, South America and the USA. Our solution partner network for sales and service is present in more than 140 countries.



- STULZ Headquarters
- Engineering & Manufacturing Facilities
- Subsidiaries
- Partners



STULZ North American Headquarters

STULZ AIR TECHNOLOGY SYSTEMS (STULZ USA), INC.

1572 Tilco Drive | Frederick, MD 21704

Tel. 301.620.2033 | Fax 301.662.5487

info@stulz-ats.com

USA
GERMANY
AUSTRALIA
AUSTRIA
BELGIUM
BRAZIL
CHINA
FRANCE
INDIA
ITALY
MEXICO
NETHERLANDS
NEW ZEALAND
POLAND
SINGAPORE
SOUTH AFRICA
SPAIN
UNITED KINGDOM

STULZ Global Headquarters

STULZ GmbH

Holsteiner Chaussee 283 | 22457

Hamburg

Tel. +49 40 5585-0 | Fax +49 40

5585-352

products@stulz.de

STULZ Subsidiaries

STULZ Australia Pty. Ltd.

34 Bearing Road

Seven Hills NSW 2147

Tel. +61 (2) 9674 4700

Fax +61 (2) 9674 6722

sales@stulz.com.au

STULZ Austria GmbH

Industriezentrum NÖ – SÜD,

Straße 15, Objekt 77, Stg. 4, Top 7

2355 Wiener Neudorf

Tel. +43 1 615 99 81-0

Fax +43 1 615 99 81-80

info@stulz.at

STULZ Belgium BVBA

Tervurenlaan 34

1040 Brussels

Tel. +32(470)292020

info@stulz.be

STULZ Brasil

Ar Condicionado Ltda.

Rua Cançioneiro de Évora, 140

Bairro - Santo Amaro São

Paulo-SP, CEP 04708-010

Tel. +55 11 4163 4989

Fax +55 11 2389 6620

comercial@stulzbrasil.com.br

STULZ España S.A.

Avenida de los Castillos 1034

28918 Leganés (Madrid)

Tel. +34(91)5178320

Fax +34(91)5178321

info@stulz.es

STULZ France S. A. R. L.

107, Chemin de Ronde

78290 Croissy-sur-Seine

Tel. +33(1)34804770

Fax +33(1)34804779

info@stulz.fr

STULZ S.p.A.

Via Torricelli, 3

37067 Valeggio sul Mincio (VR)

Tel. +39(045)633 1600

Fax +39(045) 633 1635

info@stulz.it

STULZ-CHSPL

(India) Pvt. Ltd.

006, Jagruti Industrial Estate

Mogul Lane, Mahim

Mumbai - 400016

Tel. +91 (22) 5666 9446

Fax +91 (22) 5666 9448

info@stulz.in

STULZ México S.A. de C.V.

Avda. Santa Fe No. 170

Oficina 2-2-08, German Centre

Delegación Alvaro Obregón

MX- 01210 México

Distrito Federal

Tel. +52(55)52928596

Fax +52(55)52540257

ventas@stulz.com.mx

STULZ GROEP B. V.

Postbus 75

180 AB Amstelveen

Tel. +31(20)5451111

Fax +31(20)6458764

stulz@stulz.nl

STULZ New Zealand Ltd.

Office 71, 300 Richmond Rd.

Grey Lynn, Auckland

Tel. +64(9)3603232

Fax +64(9)3602180

sales@stulz.co.nz

STULZ Polska SP. Z O.O.

Budynek Mistral.

Al. Jerozolimskie 162

02 – 342 Warszawa

Tel. +48(22)8833080

Fax +48(22)8242678

info@stulz.pl

STULZ Singapore Pte Ltd.

33 Ubi Ave 3 #03-38 Vertex

Singapore 408868

Tel. +6567492738

Fax +6567492750

andrew.peh@stulz.sg

STULZ Air Technology and Services Shanghai Co., Ltd.

Room 406, Building 5

457 North Shanxi Road

Shanghai 200040

Tel: +86 21 3360 7101

Fax: +86 21 3360 7138

info@stulz.cn

STULZ South Africa Pty. Ltd.

Unit 3, Jan Smuts Business Park

Jet Park, Boksburg

Gauteng, South Africa

Tel. +27(0)113972363

Fax +27(0)113973945

aftersales@stulz.co.za

STULZ U. K. Ltd.

First Quarter,

Blenheim Rd. Epsom

Surrey KT 19 9 QN

Tel. +44(1372)749666

Fax +44(1372)739444

sales@stulz.co.uk

Close to you around the world

STULZ has multiple manufacturing sites in Europe, North America and Asia, as

well as hundreds of subsidiaries and partners around the world.

For further information, please visit our website at www.stulz-usa.com