

MiniSpace and MiniSpace EC

Reliability for small and medium-sized IT rooms



Precision air conditioning Reliably protecting your equipment and data

Rooms subject to high thermal loads need constant climatic conditions in order to work reliably. Fluctuating temperatures, humidity and dust jeopardize both function and data stocks. The MiniSpace precision air conditioning system from STULZ cools small servers and equipment rooms with a heat load of up to 28 kilowatts. With MiniSpace, you can keep your computer systems cool more efficiently, reliably and durably than with conventional comfort air conditioning systems. These precision air conditioning units require only little floor space, and their compact size means they can be integrated in existing server rooms without problem.



Higher energy efficiency thanks to EC technology

The MiniSpace series is now also available with EC fans, to further increase energy efficiency. MiniSpace EC fans are powered as standard by energy-saving EC DC motors. The electronically controlled EC fans react steplessly to changing output requirements, run in especially energy-saving partial load mode and are insensitive to fluctuations in voltage. EC fans consume up to 30 % less energy than conventional 3-phase fans!




Maintenance-free EC fan

In general, a distinction is made between comfort and precision air conditioning. While comfort air conditioning creates a pleasant environment for people, precision air conditioning technology provides reliable cooling that is geared towards the requirements of technical infrastructure. IT rooms, data centers and switching stations require precisely controlled relative humidity, room temperature, air conduction and air distribution. Precision air conditioning units from STULZ enable you to create precisely defined climatic conditions – with pinpoint accuracy and outstanding reliability.



High operational reliability under continuous load 24/7

In contrast to comfort air conditioning, precision air conditioning is designed for high operational reliability – around the clock, 365 days a year




MiniSpace Eco-Cool with Direct Free Cooling





MiniSpace Eco-Cool units are available as downflow versions



Air distribution in Free Cooling mode

The Eco-Cool function enables Direct Free Cooling with outside air and achieves energy savings of up to 90%. MiniSpace Eco-Cool combines Free Cooling and compressor cooling in 4 stages:

Free Cooling (outside temperature between supply air set point and antifreeze temperature):

Outside air damper opens. Outside air flows through the filter directly into the unit, then into the IT room; compressor off.

Extended Free Cooling (outside temperature above supply air set point):

The cooling capacity is kept constant by increasing the air flow. Outside air damper open; compressor off

Mixed mode (outside temperature continously increasing):

If the fan reaches maximum speed and Extended Free Cooling is no longer sufficient, the compressor is switched on for support; outside air damper open; compressor runs in partial load mode.

DX mode (outside temperature is outside the suitable temperature range):

The unit works in Compressor mode; outside air damper closed.


MiniSpace – The air conditioning solution for small and medium-sized IT rooms

Advantages

- > Maximum cooling performance with minimum floor space
- > Choice of cooling with air, with water/glycol mixture or with chilled water
- > Units in downflow and upflow versions
- > Simple installation and maintenance through doors on the front
- > Air filtering with filter class EU 4
- C1002 microprocessor for climate constancy and central monitorina:
 - Adjustment of set points, control parameters and
 - All parameters are saved so that they are backed up in the event of a power failure
 - Alarms are displayed
 - Can be connected to BMS and STULZ monitoring systems

Options

- > C7000 Advanced user interface with LCD graphic display, RS485 interface and other preinstalled data protocols for connection to BMS
- > Communication via SNMP/HTTP IP protocols
- Humidifier/heater
- > Air cooled condensers
- > Winter Start Kit
- > Smoke and fire alarms
- Control of up to 20 air conditioning modules per data bus system



Remarks: All data applies at 400V/3 ph/50 Hz

¹⁾ DX cooling capacity for A and G units; return air conditions: 24°C/50 % r. h.; condensing temperature: 45°C

²⁾ CW cooling capacity for CW units; return air conditions: 24°C/50 % r. h.; water temperature: 7/12°C; glycol fraction: 0%

³⁾ Noise level at 1 m distance in free-field conditions

⁴⁾ The electric power consumption of the fans must be added to the room load ⁵⁾ Condenser for type A units with R407C; condensing temperature: 45 °C; ambient temperature: 32 °C Technical data subject to change without notice.

MiniSpace EC – Even more benefits and options with EC technology


Advantages

- > MiniSpace EC offers all the advantages and options of MiniSpace units
- > Variable-speed fan
 - High motor efficiency up to 92 % which means considerably lower operating costs
 - Quiet running, long life, maintenance-free
 - Pinpoint adjustment to the prevailing conditions
- > Filter control management for a constant air flow
- > C7000 IO controller for controlling and monitoring the air conditioning system
- Use of CW standby management
- Modbus preinstalled

Options

- > Eco-Cool with Direct Free Cooling
- > R134a high-temperature refrigerant

MORE EFFICIENCY -MORE POSSIBILITIES!



- Remarks: All data applies at 400 V/3 ph/50 Hz

 1) DX cooling capacity for A and G units; return air conditions: 24 °C, 50 % r. h.; condensing temperature 45 °C

 2) CW cooling capacity for CW units; return air conditions: 24 °C, 50 % r. h.; water temperature: 7 °C/12 °C; glycol fraction: 0 %

 3) Noise level at 1 m distance in free-field conditions

- 4) The electric power consumption of the fans must be added to the room load 5) Condenser for type A units with R407C, condensing temperature 45 °C, ambient temperature: 32 °C

Technical data subject to change without notice.

STULZ Company Headquarters

STULZ GmbH

Holsteiner Chaussee 283 · 22457 Hamburg Tel.: +49(40)55 85-0 · Fax: +49(40)55 85 352 · products@stulz.de



STULZ Subsidiaries

AUS STULZ AUSTRALIA PTY. LTD.

34 Bearing Road · Seven Hills NSW 21 47 Tel.: +61 (2) 96 74 47 00 · Fax: +61 (2) 96 74 67 22 · sales@stulz.com.au

STULZ AUSTRIA GmbH

Lamezanstraße 9 - 1230 Wien

Tel.: +43 (1) 615 99 81-0 - Fax: +43 (1) 616 02 30 - info@stulz.at

B STULZ BELGIUM BVBA

Tervurenlaan 34 - 1040 Brussels

Tel.: +32 (470) 29 20 20 · info@stulz.be

STULZ AIR TECHNOLOGY AND SERVICES SHANGHAI CO., LTD.

Room 5505, 1486 West Nanjing Road, JingAn · Shanghai 200040 · P.R. China
Tel.: +86 (21) 3360 7133 · Fax: +86 (21) 3360 7138 · info@stulz.cn

STULZ ESPAÑA S.A.

Avenida de los Castillos 1034 · 28918 Leganés (Madrid) Tel.: +34 (91) 517 83 20 · Fax: +34 (91) 517 83 21 · info@stulz.es

STULZ FRANCE S. A. R. L.

107, Chemin de Ronde - 78290 Croissy-sur-Seine

Tel.: +33 (1) 34 80 47 70 · Fax: +33 (1) 34 80 47 79 · info@stulz.fr

GB STULZ U. K. LTD.

First Quarter - Blenheim Rd. - Epsom - Surrey KT 19 9 QN

Tel.: +44 (1372) 74 96 66 · Fax: +44 (1372) 73 94 44 · sales@stulz.co.uk

STULZ S.p.A.

Via Torricelli, 3 - 37067 Valeggio sul Mincio (VR)

Tel.: +39 (045) 633 16 00 · Fax: +39 (045) 633 16 35 · info@stulz.it

STULZ-CHSPL (INDIA) PVT. LTD.

006, Jagruti Industrial Estate - Mogul Lane, Mahim - Mumbai - 400 016

Tel.: +91 (22) 56 66 94 46 · Fax: +91 (22) 56 66 94 48 · info@stulz.in

NI STULZ GROEP B. V.

Postbus 75 - 1180 AB Amstelveen

Tel.: +31 (20) 54 51 111 · Fax: +31 (20) 64 58 764 · stulz@stulz.nl

NZ STULZ NEW ZEALAND LTD.

Office 71, 300 Richmond Rd. Grey Lynn - Auckland
Tal : +64(9) 360 32 32 - Fay: +64(9) 360 21 80 - Falos@stulz.co.nz

Tel.: +64(9)360 32 32 · Fax: +64(9)360 21 80 · sales@stulz.co.nz

STULZ POLSKA SP. Z O.O.

Budynek Mistral - Al. Jerozolimskie 162 - 02 – 342 Warszawa
Tal : +48 (22) 883 30 80 - Fay: +48 (22) 824 26 78 - info@stulz p

Tel.: +48 (22) 883 30 80 · Fax: +48 (22) 824 26 78 · info@stulz.pl

SG STULZ SINGAPORE PTE LTD.

33 Ubi Ave 3 #03-38 Vertex - Singapore 408868

Tel.: +65 6749 2738 · Fax: +65 6749 2750 · andrew.peh@stulz.sg

STULZ AIR TECHNOLOGY SYSTEMS (SATS), INC.

1572 Tilco Drive - Frederick, MD 21704

Tel.: +1 (301) 620 20 33 · Fax: +1 (301) 662 54 87 · info@stulz-ats.com

TA STULZ SOUTH AFRICA PTY. LTD.

Unit 18, Jan Smuts Business Park \cdot Jet Park \cdot Boksburg \cdot Gauteng, South Africa Tel.: +27 (0)11 397 2363 \cdot Fax: +27 (0)11 397 3945 \cdot aftersales@stulz.co.za

IT Cooling Solutions

Close to you all over the world.

... With specialist, competent partners in our subsidiaries and exclusive sales and service partners around the world. Our five production sites are in Europe, North America and Asia.

